Specifications

For other materials or modifications, please consult TESCOM.

OPERATING PARAMETERS

Pressure rating per criteria of ANSI/ASME B31.3

Maximum Inlet Pressure

Stainless Steel: 10,000 psig / 690 bar

Brass: 6000 psig / 415 bar

Maximum Outlet Pressure

5-500, 5-800, 10-1500, 15-2500, 25-4000, 50-6000, 200-10,000 psig 0.3-35, 0.3-55, 0.7-105, 1-175, 1.7-275, 3.4-415, 14-690 bar

Design Proof Pressure

150% maximum rated

Leakage

Bubble-tight

Operating Temperature

-40°F to 165°F / -40°C to 74°C

Flow Capacity Standard: $C_V = 0.06$

Optional: $C_V = 0.02, 0.12, 0.30$

MEDIA CONTACT MATERIALS

Body

316 Stainless Steel or Brass

Bonnet

300 Series Stainless Steel

40 Micron Filter

300 Series Stainless Steel or Bronze

Seat

Main Valve: Vespel® Vent Valve: CTFE

Seals

Buna-N

Back-Up Rings

Teflon®

Trim

300 Series Stainless Steel

OTHER

Cleaning

CGA 4.1 and ASTM G93

Weight (without gauges)

Stainless Steel: 5.5 lbs / 2.5 kg

Brass: 5.7 lbs / 2.6 kg

Teflon®, Viton-A®, Kalrez®, and Vespel® are registered trademarks of E.I. du Pont de Nemours and Company.



TESCOM 26-1000 Series controls pressures up to 10,000 psig / 690 bar. This pressure reducing regulator offers standard venting providing decreased outlet pressure. The 26-1000 Series has an interchangeable spring and sensor for product versatility. The low torque handknob is easy to adjust.

Applications

- · Test equipment
- · Calibration stands
- Production equipment

Features and Benefits

- Can be easily converted to seven different outlet pressure ranges
- Available with captured venting
- Numerous inlet and outlet porting options
- Available in Brass or Stainless Steel
- Unbalanced stem provides positive shut-off
- Safety and reliability of piston sensor
- Excellent sensitivity through a wide range of pressure settings
- Vents to zero psiq / bar in all pressure ranges








TESCOM


26-1000 Series Regulator Drawing






26-1000 Series Regulator Flow Charts

For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.



FLOW RATE - SCFM [SLPM] Nitrogen



FLOW RATE - SCFM [SLPM] Nitrogen



TESCOM

26-1000 Series Regulator Part Number Selector



(i) Learn more about common options. For modifications, repair kits and accessories, contact factory.

Example for selecting a part number:

26-10	1	4	- 3	4	[BLANK]
BASIC SERIES	BODY MATERIAL	OUTLET PRESSURE RANGE	INLET AND OUTLET PORT TYPE	INLET AND OUTLET PORT SIZE	OPTIONS
26-10	1 – Brass 6 – 316 Stainless Steel	1 – 200-10,000 psig 14-690 bar (Stainless Steel Body Only) 2 – 50-6000 psig 3.4-415 bar 3 – 25-4000 psig 1.7-275 bar 4 – 15-2500 psig 1-175 bar 5 – 10-1500 psig 0.7-105 bar 6 – 5-800 psig 0.3-55 bar 7 – 5-500 psig 0.3-35 bar	1 – SAE¹ (SAR¹ for Europe) 2 – NPTF 3 – MS33649¹ 4 – High Pressure 6 – Medium Pressure 1. Two inlet and outlet ports standard at 90°	4 – 1/4" 6 – 3/8" (NPTF only)	[BLANK] – None 005 – Viton-A® O-rings 008 – 1/4* NPTF inlet and outlet gauge ports 045 – Non-venting 163 – 1/2* inlet and outlet ports 249 – 15,000 psig / 1034 bar inlet capability (Stainless Steel model only)



26-1000 Series Regulator Standard Modifications

MODIFICATION				FEATUREPART NUMBER SUFFIX
Captured Venting				002
The captured bonnet vent po	ort allows the user to: 1) capture	e fluids, 2) re-u	ise vented media, and 3) provide	a secondary sealed barrier.
Standard Unit with Viton-A	N® Soft Goods			005
Captured Venting with Vito	on-A® Soft Goods			
1/4" NPTF Inlet and Outlet	Gauge Ports at 60° Angle			008
15,000 psig / 1034 bar Inle	t and Outlet Pressure Capa	bilities in St	ainless Steel	039
For varied outlet capabilitie	s, consult factory.			
Wrench Adjustment with L	ocking Device			098
For applications subject to v	ibration or accidental change	s in pressure	settings.	
1/2" Inlet and Outlet Ports				163
Non-Venting with Viton-A	O-Rings			280
Air Ratio Device, Non-Vent	ing Only			045A
With pressure ranges of:				
Model Number	Max. P2 / psig	Ratio*	Notes	
26-10X1-XX-045A	10,000 / 690 bar	125-1	Stainless Steel Only	
26-10X2-XX-045A	6000 / 414 bar	75-1	Brass or Stainless Steel	
26-10X4-XX-045A	2500 / 172 bar	32-1	Brass or Stainless Steel	TESCON THE PROPERTY OF THE PRO
26-10X5-XX-045A	1500 / 103 bar	19-1	Brass or Stainless Steel	O 26-1000 with
* Ratio is for reference only				Air Actuator
Seat Material: Teflon®, CTFE	E, PEEK®, 17-4 PH Stainless S	teel		consult TESCOM
O-Ring Material: Teflon®, Vi	ton-A®, Ethylene Propylene,	Urethane, K	alrez®	consult TESCOM
Vent Options: Captured Bor	nnet, Non-Venting			consult TESCOM
Loading Options:				
Air Ratio**, Dome-Load (1:1), Bias: captured bonnet (negative or	positive bias), Wrench Adjust	consult TESCOM
* * The air ratio model can	provide up to 15,000 psig / 10	34 bar outlet	t pressure. For specific ratios, co	onsult factory.
Pressures: 20,000 psig / 137	9 bar inlet and outlet			consult TESCOM
Flow Capacity: $C_V = 0.12$, C_V	_v = 0.02 (not available with m	netal seat)		consult TESCOM
Cartridge Mounted				consult TESCOM
Electronic Controls				consult TESCOM
Available to automate your	system. Can be used with air	ratio or dome	e-loaded models	

26-1000 Series Regulator Accessories (optional at extra cost)

ITEM	PART NUMBER
Gauges Consult GAUGES section of catalog	
Standard Repair Kit	P/N 38-1000-26
Standard Soft Goods Kits:	
Model: 26-10X1	P/N 389-1016
26-10X2 and 26-10X3	P/N 389-1005
26-10X4	P/N 389-1017
26-10X5, 26-10X6, and 26-10X7	P/N 389-1002
Consult Tescom about kits for modifications.	
Multiple Range Kit (see back page)	P/N 38-100X-XXX-X>
Main Valve Service Tool.	P/N 6557-3



26-1000 Multiple Range Kits

TESCOM's Multiple Range Kits permit the 26-1000 Series to be modified to any one of several different outlet pressure ranges. Modular design of these regulators permit the outlet pressure ranges to be changed while retaining the desirable characteristics of minimum lock-up, maximum sensitivity, precision and accuracy.

This can be done by interchanging a combination of sensors and load springs and can be accomplished while the regulator remains in line and connected to the system.

With the use of the Multiple Range Kits, the 26-1000 Series regulator has the ability to accomplish what would ordinarily require up to seven different regulators.

To change the pressure range, simply remove the control knob which is retained by a locknut, unscrew the bonnet $(1\ ^3/4"$ across the flats for the 26-1000) and remove the spring and sensor. Select the spring and sensor combination which will produce the pressure range required. Reassemble the regulator and resume regulator operation.

- Economy and convenience of a single regulator
- Modular components
- Minimum lock-up with maximum sensitivity
- Convert without removing from panel
- Color coded springs
- No special tools involved

26-1000 Series Kit



Desired Outlet	26-1000 SERIES				
Pressure Range	Sensor Assy. No.	Sensor P/N	Spring Color	Spring P/N	
200-10,000 psig / 14-690 bar	1	1006-XX	Silver	1051	
50-6000 psig / 3.4-414 bar	2	1007-XX	Silver	1051	
25-4000 psig / 1.7-276 bar	2	1007-XX	Gold	1050	
15-2500 psig / 1.0-172 bar	3	1008-XX	Silver	1051	
10-1500 psig / 0.7-103 bar	4	1009-XX	Silver	1051	
0-800 psig / 0-54 bar	4	1009-XX	Gold	1050	
0-500 psig / 0-35 bar	4	1009-XX	Olive	1049	

Since the 26-1000 regulator is provided with one spring and one sensor when shipped, the Multiple Range Kit will contain all other springs and sensors required to accomplish any of the above listed pressures ranges.

Part Number Selector for Multiple Range Kits

Example for selecting a part number:

26-1000 SERIES

38-100	Х -	XXX	X	X
BASIC SERIES	SPRING COMBINATION	SENSOR ASSEMBLY NUMBERS	METALLIC MATERIAL	O-RING MATERIAL
38-100	1 – 1049-1050 2 – 1049-1051 3 – 1050-1051	1 2 3 4	2 – 300 Series Stainless Steel 6 – 316 Stainless Steel	0 – Buna-N 2 – Viton-A [®] 5 – Ethylene Propylene



WARNING! Do not attempt to select, install, use or maintain this product until you have read and fully understood the TESCOM Safety, Installation and Operation Precautions.

D26100538X012 \bigcirc 2015, 2017 Emerson Process Management Regulator Technologies, Inc. All rights reserved. 08/2017. Tescom, Emerson Process Management, and the Emerson Process Management design are marks of one of the Emerson Process Management group of companies. All other marks are the property of their respective owners.



