Specifications

For other materials or modifications, please consult TESCOM.

OPERATING PARAMETERS

Pressure rating per criteria of ANSI/ASME B31.3

Maximum Inlet Pressure

600 or 3500 psig / 41.4 or 241 bar

Outlet Pressure Ranges

0-30, 0-60, 0-100, 0-150 and 250 psig 0-2.1, 0-4.1, 0-6.9, 0-10.3 and 17.2 bar

Design Proof Pressure

150% of maximum rated

Inboard Leak Rate

1 x 10⁻⁹ atm cc/sec He

Operating Temperature

PTCFE Seat: -40°F to 140°F / -40°C to 60°C Teflon® Seat: -40°F to 160°F / -40°C to 71°C Vespel® Seat: -40°F to 350°F / -40°C to 177°C

Flow Capacity

 $C_V = 0.06 (3500 \text{ psig} / 241 \text{ bar model})$ $C_V = 0.15 (600 \text{ psig} / 41.4 \text{ bar model})$

Decaying Inlet Characteristic

 $C_v = 0.06$: 0.7 per 100 psig / 0.05 per 6.9 bar

MEDIA CONTACT MATERIALS

Body

316L Stainless Steel Electropolish or 316L VAR Stainless Steel Electropolish

Diaphragm

316L Stainless Steel or Hastelloy®

Seat

PCTFE or Teflon® (Vespel® optional for 3500 psig / 241 bar model only)

Spring

316 Stainless Steel or Eligiloy®

Stem, Seat Retainer, Valve Guide

316 Stainless Steel or Hastelloy®*

OTHER

Internal Surface Finish

10 Ra microinch / 0.25 micrometer

Connections

Welded female or male VCR®

Tube stubs

High Purity Internal Connections (H.P.I.C.)

(Internal style of VCR®, compatible with male swivel VCR®)

Cleaning

DI water electronic grade cleaned and ES 500 Particle Certified for internal electropolish models

Internal Volume

1/4" fitting / 5.75 cc

Weight (without gauges)

2 lbs / 0.9 kg

Teflon® and Vespel® are registered trademarks of E.I. du Pont de Nemours and Company.

Hastelloy® is a registered trademark of Haynes International, Inc. Elgiloy® is a registered trademark of Elgiloy Corp. VCR® is a registered trademark of Cajon Co.

*Material to be Hastelloy® or equivalent per ASTM B 574



TESCOM 64-2600 Series economical high purity pressure reducing regulator provides Stainless Steel construction with $10\,R_a$ surface finish and is electronic grade cleaned. Inlet pressures are 600 or 3500 psig / 41.4 or 241 bar with outlet pressures of up to 250 psig / 17.2 bar.

Applications

- 1/4" point-of-use
- Gas cabinets
- Semiconductor manufacturing
- Valve manifold boxes
- Research labs

Features and Benefits

- Optimum performance and cleanliness at a great value
- Internal surface finished to 10 R_a microinch / 0.25 micrometer ensures minimal particle generation or entrapment
- True metal-to-metal body diaphragm seal provides enhanced leak integrity
- No bias spring or friction device in the flow stream
- · Adjustable stop to limit outlet pressure
- Positionable ported bonnet ring is available








TESCOM

64-2600 Series Regulator Drawing








64-2600 Series Regulator Flow Chart

For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.



FLOW RATE - SCFM [SLPM] Nitrogen





64-2600 Series Regulator Part Number Selector

Repair Kits, Accessories & Modifications may be available for this product. Please contact TESCOM for more information.

Example for selecting a part number:

64-26	4	2	K	A4		1	0	
BASIC SERIES	BODY MATERIAL/ FINISH	OUTLET PRESSURE RANGES	SEAT MATERIAL	INLET AND OUTLET PORT SIZE AND TYPE	'A' ± .06"	MAXIMUM INLET	GAUGE PORT OPTION	NO. OF GAUGE PORTS (SEE FIGURE)
64-26	 4 - 316L Stainless Steel Electropolish: 10 R_a¹ 6 - 316L VAR Stainless Steel Electropolish: 10 R_a² 1. Per ASTM B 912 2. Per SEMI F19, HP grade 	 0 - 0-30 psig	K – PCTFE T – Teflon® V – Vespel® (3500 psig / 241 bar model only)	A4 – 1/4" H.P.I.C. RK – 1/2" Male Swivel RL – 1/2" Female Swivel RM – 1/4" Male Swivel RU – IN Port:1/4" Male; OUT Port: 1/4" Female RV – IN Port:1/4" Female; OUT Port: 1/4" Alale T4 – 1/4" Tube Stubs	- 4.75" 4.75" 3.70" 3.70" 3.70" 3.70"	1 - 3500 psig 241 bar 316 Stainless Steel Trim 2 - 600 psig 41.4 bar 316 Stainless Steel Trim 3 - 3500 psig 241 bar Hastelloy® Trim 4 - 600 psig 41.4 bar Hastelloy® Trim	 0 - None 1 - 1/4" H.P.I.C. 2 - 1/4" H.P.I.C. 3 - 1/4" H.P.I.C. 4 - 1/4" Male Swivel 5 - 1/4" Male Swivel 6 - 1/4" Male Swivel 7 - 1/4" Female Swivel 8 - 1/4" Female Swivel 9 - 1/4" Female Swivel 5 - 1/4" Fixed Male T - 1/4" Fixed Male U - 1/4" Fixed Male 	2 (Figure B) 2 (Figure D) 2 (Figure D) 1 (Figure C) 2 (Figure B) 2 (Figure D) 1 (Figure C)

 \triangle

WARNING! Do not attempt to select, install, use or maintain this product until you have read and fully understood the TESCOM Safety, Installation and Operation Precautions.

