## **Specifications**

For other materials or modifications, please consult TESCOM.

### **OPERATING PARAMETERS**

Pressure rating per criteria of ANSI/ASME B31.3

#### **Maximum Inlet Pressure**

500, 3000 psig / 34.5, 207 bar

#### **Outlet Pressure Ranges**

0-25, 0-50, 0-100, 0-150, 0-200 psig 0-1.7, 0-3.4, 0-6.9, 0-10.3, 0-13.8 bar

#### **Design Proof Pressure**

150% of rated pressure

#### Leakage

Internal: Bubble-tight

External: < 2 x 10<sup>-8</sup> atm cc/sec He

#### **Operating Temperature**

-40°F to 140°F / -40°C to 60°C

#### **Flow Capacity**

 $C_{V} = 1.0$ 

C<sub>V</sub> = 1.8 (Optional)

### MEDIA CONTACT MATERIALS

### Body

Brass, 316 Stainless Steel

#### **Bonnet**

300 Series Stainless Steel

#### Diaphragm

316 Stainless Steel

### Seat

3000 psig / 207 bar Inlet: CTFE 500 psig / 34.5 bar Inlet: Teflon®

### Seat Retainer

Nitronic 60

## Seal

Teflon®

#### **Remaining Parts**

316 Stainless Steel

### OTHER

## Cleaning

CGA 4.1 and ASTM G93

## Weight (without gauges)

3.5 lbs / 1.6 kg

Teflon® is a registered trademark of E.I du Pont de Nemours and Company.



TESCOM 44-3200 Series is a compact, high flow, high purity single-stage regulator for specialty, flammable and industrial gas flows of 5-50 SCFM / 141-1415 SLPM. Diffusion-resistant metal diaphragm seal ensures gas purity and integrity.

## **Applications**

- Laboratory and point-of-use gas systems
- Laser assist and resonator gases
- Glove box and isolators

## **Features and Benefits**

- Available in 316 Stainless Steel or Brass
- Choice of inlet pressure ratings: 500 or 3000 psig / 34.5 or 207 bar maximum
- True metal-to-metal diaphragm seal to minimize diffusion
- Five outlet pressure ranges are available
- Gauge ports are standard
- Optional high flow model (C<sub>V</sub> = 1.8) is available
- Panel mounting is optional
- · Non-venting is standard








## TESCOM


# 44-3200 Series Regulator Drawing






## 44-3200 Series Regulator Flow Charts

For more information on how to read flow curves, please refer to the Flow Curves and Calculations document (debul2007x012) in the TESCOM catalog or on www.tescom.com.



FLOW RATE - SCFM [SLPM] Air  $C_V = 1.0$ 



FLOW RATE - SCFM [SLPM] Air  $C_V = 1.0$ 



# 44-3200 Series Regulator Part Number Selector

**Learn more about common options.**For modifications, repair kits and accessories, contact factory.

Example for selecting a part number:

44-3	2 6	1		J	2	8	1	
BASI SERII	R( ) I ) V I / I A I F R I A I	OUTLET PRESSURE RANGES	SOFT GOODS SEAT SEAL		INLET AND OUTLET PORT TYPE	INLET AND OUTLET PORT SIZE	MAXIMUM INLET PRESSURE	OPTIONS
44-3	2 1 – Brass 6 – 316 Stainless Steel	<ul> <li>0 - 0-25 psig 0-1.7 bar</li> <li>1 - 0-50 psig 0-3.4 bar</li> <li>2 - 0-100 psig 0-6.9 bar</li> <li>3 - 0-150 psig 0-10.3 bar</li> <li>4 - 0-200 psig 0-13.8 bar</li> </ul>	H – Teflon® J – CTFE	Teflon®, O-ring Teflon®, Spring Energized Lip Seal	2 - NPTF	6 – 3/8" 8 – 1/2"	1 – 3000 psig 207 bar 3 – 500 psig 34.5 bar	-001 – One 1/4" gauge port at 90°, $C_V$ = 1.0 -003 – No gauge ports -296 – One 1/4" gauge port at 90°, $C_V$ = 1.8

WARNING! Do not attempt to select, install, use or maintain this product until you have read and fully understood the TESCOM Safety, Installation and Operation Precautions.

